

4 mm Banana (female) Jack (socket) w/ M4 Threaded Stud and Hex Nuts



Features

- IP2X touchproof protection and double port
- Compliant with shrouded 4 mm banana plugs

Applications

- To repair or make panels or boxes providing heavy duty and safety
- 4 mm banana connections for power supplies, measurements, controls, tests



Specification

Electrical protection	1000 V CAT II / 1000 V CAT III / 600 V CAT IV, reinforced insulation, pollution degree 1 or 2, up to 25 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour
RND 350-00065	Black
RND 350-00066	Red
RND 350-00067	Blue
RND 350-00068	Yellow/ Green
RND 350-00069	Yellow
RND 350-00070	Green

