

Test Lead Kit 8 PCS



As the set includes several finished products
please refer to the safety of each part number
The set includes the part numbers below

Stacking 4 mm Banana (male) Plug to Stacking 4 mm Banana (male) Plug Leads

Applications

To connect to 4 mm banana jacks, sockets, and binding posts
Very low voltage general purpose electric testing, controlling, and measuring

Specification

Electrical protection	30V AC / 60V DC , 36 A
Operating Temperature Range	-20 °C...+80 °C
Length	1 m
Colour	Black / Red

RND Part Nr. RND 350-00106 (Black)

RND Part Nr. RND 350-00107 (Red)



RND 350-00106



RND 350-00107

Alligator Clips with 4mm Banana Socket

Features

Optimum jaw design to clench well a lot of various items as bar, wire, screw, PCB pin etc.
IP2X touchproof protection on the jaws when closed and the 4 mm banana female to prevent accidental contact
The clip is designed to reduce the risk of short-circuits and arc flashes
For this purpose the metal jaws can not be touched when closed (IP2X)
Protective fingerguard
Keep behind the protective fingerguard to operate safely the clip while connecting to hazardous live voltages

Applications

To grasp conductive parts safely
General purpose electric and electronic testing, controlling and measuring

Specification

Electrical protection	1500 V/1000 V AC CAT II / 1000 V CAT III / 600 V CAT IV, reinforced insulation, pollution degree 1 or 2 , 20 A
Operating Temperature Range	-20 °C...+60 °C
Colour	Black / Red

RND Part Nr. RND 350-00121 (Black)

RND Part Nr. RND 350-00122 (Red)



RND 350-00121



RND 350-00122

Sharp Steel Tip Probes with 4mm Banana Socket

Features

Probe is provided with a removable insulating sleeve which covers the tip
Sharp steel tip to scrape coatings
The flat surface on the $\varnothing 22$ mm flange prevents the probe from rolling on a table

Applications

To measure voltages up to 1000 V CAT IV on contacts which are small, difficult to access, remote, coated with oxidation, paint, dust, enamel etc.

Specification

Electrical protection	1000 V CAT II / 1000 V CAT III / 1000 V CAT IV, reinforced insulation, pollution degree 1, 2 or 3, 16 A
Operating Temperature Range	-20 °C...+80 °C
Colour	Black / Red
RND Part Nr.	RND 350-00109 (Black)
RND Part Nr.	RND 350-00110 (Red)



RND 350-00109



RND 350-00110

Pincer Clips with 4mm Banana Socket

Features

Long and flexible thin stem to access to deep target items while dense environments
Handling is eased by the syringe-type ergonomics

Applications

To grasp conductive parts safely to measure voltages
General purpose electric and electronic testing, controlling and measuring

Specification

Electrical protection	1000 V CAT II, reinforced insulation, pollution degree 1 or 2, 6 A
Operating Temperature Range	-20 °C...+80 °C
Colour	Black / Red
RND Part Nr.	RND 350-00115(Black)
RND Part Nr.	RND 350-00116 (Red)



RND 350-00115



RND 350-00116