

Sharp Steel Tip Probe Body w/ 4 mm Banana (female) Jack



Features

Probe is provided with a removable insulating sleeve which covers the tip

Sharp steel tip to scrape coatings

The flat surface on the $\varnothing 22$ mm flange prevents the probe from rolling on a table



Applications

To measure voltages up to 1000 V CAT IV on contacts which are small, difficult to access, remote, coated with oxidation, paint, dust, enamel etc.

Specification

Electrical protection	1000 V CAT II / 1000 V CAT III / 1000 V CAT IV, reinforced insulation, pollution degree 1, 2 or 3, 16 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour
RND 350-00109	Black
RND 350-00110	Red

