

Connecting 4 mm Banana Tip Probe Body w/ 4 mm Banana (female) Jack



Features

The flat surface on the $\varnothing 19$ mm flange prevents the probe from rolling on a table

The 4 mm banana tip allows measurements on AC power sockets



Applications

To measure safely voltages on AC power sockets

Specification

Electrical protection	1000 V CAT II , reinforced insulation, pollution degree 1 or 2 , 36 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour
RND 350-00111	Black
RND 350-00112	Red

