

# 2 mm Smooth Tip Probe Body w/ 4 mm Banana (female) Jack



## Features

The flat surface on the  $\varnothing 19$  mm flange prevents the probe from rolling on a table

The thin and long conductive tip allows measurements on deep and small contacts



## Applications

To measure voltages up to 1000 V

General purpose electric and electronic testing, controlling, and measuring

## Specification

|                             |   |
|-----------------------------|---|
| Electrical protection       | 1000 V CAT II , reinforced insulation, pollution degree 1 or 2 , 36 A |
| Operating Temperature Range | -20 °C...+80 °C   |

| RND Part Nr.  | Colour |
|---------------|--------|
| RND 350-00113 | Black  |
| RND 350-00114 | Red    |

