

# Pincer Clip w/ 4 mm Banana (female) Jack (socket)



## Features

Long and flexible thin stem to access to deep target items while dense environments

Handling is eased by the syringe-type ergonomics

## Applications

To grasp conductive parts safely to measure voltages

General purpose electric and electronic testing, controlling and measuring



## Specification

Electrical protection	1000 V CAT II , reinforced insulation, pollution degree 1 or 2 , 6 A
Operating Temperature Range	-20 °C...+80 °C

RND Part Nr.	Colour
RND 350-00115	Black
RND 350-00116	Red

