

Borescope, 640x480, Ø 8mm

Features

Ergonomic handle
180 degree rotating function
3 times zoom in function
Supports snap shots and videos recording
Can be extended with many different camera (VGA) probe accessories

Specification

Camera diameter	8.0mm
Camera light source	White LEDs 4pcs
Camera resolution	640 X 480 Pixels
Camera field of view	54°
Camera depth of field	3-6cm
Display resolution	960 X 240 Pixels
Display size	2.4"
Display rotating	180° X 2
Zoom	Digital 3 times
IP coverage	IP67 (Camera head & Probe only)
Power supply	AA 1.5V batteries x 4pcs
Probe diameter	6.5mm +/-2mm
Probe length	100cm +/-2cm
Operating temperature	0 to 45°C
Storage temperature	-10 to 50°C

Accessories

Camera probe
Magnet
Hook
Mirror
Storage case
USB cable
Operating manual

Art. Nr.
RND 355-00004

