

Borescope, 640x480, Ø 8mm, IP67



Features

Ergonomic handle

180 degree rotating function

4 times zoom in function

Supports snap shots and videos recording

Supports SD card up to 32G

Can be extended with many different camera (VGA) probe accessories

Specification

| | |
|-----------------------|---------------------------------|
| Camera diameter | 8.0mm |
| Camera light source | White LEDs x 4pcs |
| Camera resolution | 640 X 480 Pixels |
| Camera field of view | 54° |
| Camera depth of field | 3-6cm |
| Display resolution | 960 x 240 Pixels |
| Display size | 2.7" |
| Display rotating | 180° X 2 |
| IP coverage | IP67 (Camera head & Probe only) |
| Power supply | AA 1.5V batteries x 4pcs |
| Probe diameter | 6.5mm+/-2mm |
| Probe length | 100cm +/-2cm |
| Operating temperature | 0 to 45°C |
| Storage temperature | -10 to 50°C |
| Zoom | Digital 4 times |



Accessories

Camera probe

Magnet

Hook

Mirror

Storage case

USB cable

Operating manual

Art. Nr.
RND 355-00006