

Autoranging Digital Multimeter



Features

- 4000 Digital display counts
- Safety design
- Relative zero
- Data hold
- Auto power OFF
- NCV function



Specifications

| Function | Max. Range | Basic Accuracy |
|-------------|--------------|----------------|
| Voltage DC | 1000 V | ±0.5% |
| Voltage AC | 1000V | ±0.8% |
| Current DC | 10A | ±1.2% |
| Current AC | 10A | ±1.8% |
| Resistance | 40MΩ | ±0.8% |
| Duty Cycle | 99.9% | ±1.2% |
| Frequency | 10MHz | ±1.5% |
| Capacitance | 100μF/40mF | ±3.0% |
| Temperature | 760°C/1400°F | ±3.0% |

Diode Check

Continuity Test

Size (H x W x D) - 170 x 79 x 50 mm

Weight: 366 g

Safety Conformance

- EN61010-1 CAT IV 600V, CAT III 1000V
- 1000 V input protection on all ranges
- 10A/1000V & 0.5A/1000V fuses protection on current ranges

Accessories

Test leads, 9V battery, type K temperature probe



EMC & LVD

EN: 61326

EN: 61010-1

EN: 61010-02-032

EN: 61010-02-033



Art. Nr.
RND 355-00011