

# Autoranging AC / DC Clamp Meter



## Features

- With small body and jaw design for perfect handhold and tight place testing
- A large backlight display is easy to see and a handy Display Hold keeps measurements on the display
- Measuring starting current for motors, lighting, etc.
- Double molded plastic housing
- Auto power OFF
- AC / DC current measurement, 10 mA max resolution
- 4000 LCD display counts
- Data hold
- Zero function
- Low battery indication
- 30 mm jaw opening



EMC & LVD  
EN: 61326  
EN: 61010-1  
EN: 61010-02-032  
EN: 61010-02-033



## Specifications

Function	Max. Range	Basic Accuracy
Voltage DC	600 V	$\pm(0.5\%+1d)$
Voltage AC	600 V	$\pm(1.5\%+2d)$
Current DC	400 A	$\pm(2.0\%+5d)$
Current AC	400 A	$\pm(2.5\%+4d)$
Resistance	40 M $\Omega$	$\pm(3.0\%+5d)$
Frequency	10 MHz	$\pm(1.2\%+2d)$
Capacitance	100 $\mu$ F	$\pm(2.5\%+5d)$
Continuity Check	Buzzer sounds at 50 $\Omega$	
Diode Test	Test current 0.3mA	

Size (H x W x D) - 197 x 70 x 40 mm

Weight: 183 g

## Accessories

Test leads, carrying case, 2x AAA batteries

Art. Nr.

RND 365-00008