

Autoranging AC / DC Clamp Meter



Features

- The bodies and jaws fit perfectly in your hand and into tight places
- A large backlight display is easy to see and a handy Display Hold keeps measurements on the display
- True RMS measurement for ACV & ACA
- Double molded plastic housing
- Auto power OFF
- AC / DC current measurement
- 6000 LCD display counts
- Flashlight
- Peak hold
- Max /Min
- REL (Zero) function
- Auto power OFF
- Low battery indication
- Analog bargraph / 61 seg.
- 1.9" (48mm) jaw opening
- NCV detection & flashlight
- Inrush current



EMC & LVD

EN: 61326

EN: 61010-1

EN: 61010-02-032

EN: 61010-02-033



Specifications

Function	Max. Range	Basic Accuracy
Voltage DC	1000 V	$\pm(0.5\%+1d)$
Voltage AC	1000 V	$\pm(1.5\%+2d)$
Current DC	1000 A	$\pm(2.0\%+5d)$
Current AC	1000 A	$\pm(2.5\%+4d)$
Resistance	60 M Ω	$\pm(3.0\%+5d)$
Temperature	1000 °C / 1832°F	$\pm(1.0\%+3^{\circ}C)$
Capacitance	6000 uF	$\pm(2.5\%+5d)$
Frequency	10 MHz	$\pm(1.2\%+2d)$
Continuity Check	Buzzer sounds less than 50 Ω	
Diode Test	Test current 0.3mA	

Size (H x W x D) - 230 x 76 x 40 mm

Weight: 315 g

Accessories

Test leads, carrying case, temperature probe, 9 V battery

Art. Nr.

RND 365-00009