

Insulated Exposed Junction Thermocouple Type T 1m



Features

- Fast response
- Ideal for Test & Development applications
- Welded exposed junction



Specification

Sensor Type	Exposed Junction
Thermocouple Type	T
Cable Length	1 m
Cable Type	Twin-Twisted Lead
Insulation	PTFE
Conductors	1
Conductor Cross Section	0.315 mm ²
Termination Type	Miniature Flat Pin Plug Colour Coded in Accordance IEC 584
Max. Temperature	+260 °C
Min. Temperature	-75 °C
Tolerance	Class 1
Standards Met	IEC-584-3
Connector Type	Mini Plug

Art. Nr.
RND 410-00106