


# Insulated Exposed Junction Open End Type T 5m



## Features

- Fast response
- Welded exposed junction



## Specification

Thermocouple Type	T
Thermocouple Junction	Exposed
Cable Length	5 m
Cable Type	Twin-Twisted Lead
Insulation	PFA
Conductors	1
Conductor Cross Section	0.315 mm <sup>2</sup>
Cable Termination	Open End
Max. Temperature	+250 °C
Min. Temperature	-75 °C
Standards Met	ANSI MC96.1

**Art. Nr.**  
**RND 410-00107**