

# Thermocouple Probe Glassfibre Type J 2m Stainless Steel Overbraid



## Features

- Rugged thermocouple with stainless steel sheath
- Stainless steel probe sheath for protection against corrosion
- Grounded measuring junction



## Specification

Thermocouple Type	J
Thermocouple Junction	Grounded Hot Junction for fast response
Probe Diameter	4.5 mm
Probe Length	150 mm
Cable Length	2 m
Cable Type	Stainless Steel Overbraid
Insulation	Glassfibre
Conductors	7
Conductor Cross Section	0.219 mm <sup>2</sup>
Termination Type	Open End
Max. Temperature	+350 °C
Min. Temperature	-60 °C

**Art. Nr.**

**RND 410-00119**