

# Hypodermic Tip Thermocouple Type T 1.5m



## Features

- Type 'T' rigid stem, chisel point thermocouple
- Grounded hot junction
- Fast responding
- Can be used for semi-solid materials (food, plastics, rubber etc.)



## Specification

Sensor Type	Chisel Point Thermocouple
Thermocouple Type	T
Thermocouple Junction	Grounded Hot Junction
Probe Diameter	1.6 mm
Probe Length	100 mm
Sheath Material	316 Stainless Steel Sheath
Cable Length	1.5 m
Cable Type	PTFE
Conductor Cross Section	7
Conductors	0.219 mm <sup>2</sup>
Termination Type	Open End (+Brown/-White)
Max. Temperature	250 °C
Min. Temperature	-75 °C

**Art. Nr.**  
**RND 410-00122**