

Melt Bolt Thermocouple Type J 76mm Bolt Length



Features

- Designed to withstand high pressure applications
- Experienced with molten plastics & polymers



Specification

Sensor Type	Typically used in Plastics Extruders and Injection Moulders
Thermocouple Type	J
Thermocouple Junction	Insulated Hot Junction
Probe Diameter	3 mm
Probe Length	5 mm (76 mm bolt length)
Sheath Material	Stainless Steel
Termination Type	Standard Plug Termination (round pin)
Max. Temperature	+500 °C
Tolerance	Tolerance & Colour Code in Accordance with IEC-584 specification
Thread	1/2" UNF-20 Thread

Art. Nr.

RND 410-00125