Insulated Thermocouple Type K Compact Terminal Head 6mm 150mm



Features

- Flexible mineral insulated probe with 310 stainless steel sheath
- Highly flexible, sheath can be bent/formed to suit many applications and processes
- The material is good corrosion and oxidation resistance to suit a wide range of processes, satisfactorily operates in sulphur bearing atmospheres



Specification

Thermocouple Type	K
Thermocouple Junction	Insulated Hot Junction
Element/Hot Junction	Single Element, Junction Insulated from Sheath (offers protection against spurious electrical signals)
Probe Diameter	6.0 mm Diameter x 150 mm Length
Sheath Material	310 Stainless Steel Sheath
Head Type	Cast Aluminium finish
Gland	M16 x 1.5 mm Plated Brass Gland Fitted
Max. Temperature	+1100 °C (Max temp of head is 170 °C)
Min. Temperature	-40 °C
IP Rating	IP67

Art. Nr. RND 410-00160