

# Polyurethane (PU) Tubing

## Features

- Excellent pressure resistance
- Weather resistance
- Corrosion & vibration resistance
- Typical applications include:
  - Industrial Automation
  - Pneumatic Tools



## Specification

Material Polyurethane (PU)

Operating Temperature -20 ~ +80 °C

## Product Range

Art Nr.	O.D. mm	I.D. mm	Length per spool (M)	Min. bend radius at 20°C	Operating Pressure (kPa)	Bursting Pressure (kPa) (20°C)	Tubing Colour
RND 425-00031	4.0	2.5	200	20	800	2400	Blue
RND 425-00032	6.0	4.0	200	27	1000	3000	Blue
RND 425-00033	8.0	5.0	100	33	1000	3000	Blue
RND 425-00034	8.0	6.0	100	38	600	1800	Blue
RND 425-00035	8.0	5.5	100	33	800	2400	Blue
RND 425-00036	10.0	8.0	100	42	500	1500	Blue
RND 425-00037	10.0	6.5	100	37	1000	2800	Blue
RND 425-00038	12.0	10.0	100	45	400	1300	Blue
RND 425-00039	12.0	8.0	100	40	1000	2800	Blue
RND 425-00040	4.0	2.5	200	20	800	2400	Orange
RND 425-00041	6.0	4.0	200	27	1000	3000	Orange
RND 425-00042	8.0	5.0	100	33	1000	3800	Orange
RND 425-00043	8.0	6.0	100	38	600	1800	Orange
RND 425-00044	8.0	5.5	100	33	800	2400	Orange
RND 425-00045	10.0	8.0	100	42	500	1500	Orange
RND 425-00046	10.0	6.5	100	37	1000	2800	Orange
RND 425-00047	12.0	10.0	100	45	400	1300	Orange
RND 425-00048	12.0	8.0	100	40	1000	2800	Orange
RND 425-00049	4.0	2.5	200	20	800	2400	Black
RND 425-00050	6.0	4.0	200	27	1000	3000	Black
RND 425-00051	8.0	5.0	100	33	1000	3000	Black
RND 425-00052	8.0	6.0	100	38	600	1800	Black
RND 425-00053	8.0	5.5	100	33	800	2400	Black
RND 425-00054	10.0	8.0	100	42	500	1500	Black
RND 425-00055	10.0	6.5	100	37	1000	2800	Black
RND 425-00056	12.0	10	100	45	400	1300	Black
RND 425-00057	12.0	8.0	100	40	1000	2800	Black
RND 425-00058	4.0	2.5	200	20	800	2400	Transparent
RND 425-00059	6.0	4.0	200	27	1000	3000	Transparent
RND 425-00060	8.0	5.0	100	33	1000	3000	Transparent
RND 425-00061	8.0	6.0	100	38	600	1800	Transparent
RND 425-00062	8.0	5.5	100	33	800	2400	Transparent
RND 425-00063	10.0	8.0	100	42	500	1500	Transparent
RND 425-00064	10.0	6.5	100	37	1000	2800	Transparent
RND 425-00065	12.0	10.0	100	45	400	1300	Transparent
RND 425-00066	12.0	8.0	100	40	1000	2800	Transparent