

Polyamide (PA 12) Tubing



Features

- Excellent pressure resistance
- Weather resistance
- Corrosion & vibration resistance
- Typical applications include:
 - Industrial Automation
 - Pneumatic Tools



Specification

Material	Polyamide (PA 12)
Operating Temperature	-20 ~ +80 °C

Product Range

Art Nr.	O.D. mm	I.D. mm	Length per reel (M)	Bending radius at 20°C	Operating Pressure (kPa)	Bursting Pressure (kPa) (20°C)	Tubing Colour
RND 425-00067	4.0	2.0	200	30	3500	6800	Blue
RND 425-00068	6.0	4.0	200	37	2500	8100	Blue
RND 425-00069	8.0	5.0	100	48	1900	5700	Blue
RND 425-00070	10.0	8.0	100	62	1600	4500	Blue
RND 425-00071	10.0	7.5	100	60	1900	5700	Blue
RND 425-00072	12.0	9.0	100	67	1900	5700	Blue
RND 425-00073	4.0	2.0	200	30	3500	6800	Red
RND 425-00074	6.0	4.0	200	37	2700	8100	Red
RND 425-00075	8.0	5.0	100	48	1900	5700	Red
RND 425-00076	10.0	8.0	100	62	1600	4500	Red
RND 425-00077	10.0	7.5	100	60	1900	5700	Red
RND 425-00078	12.0	9.0	100	67	1900	5700	Red
RND 425-00079	4.0	2.0	200	30	3500	6800	Black
RND 425-00080	6.0	4.0	200	37	2700	8100	Black
RND 425-00081	8.0	5.0	100	48	1900	5700	Black
RND 425-00082	10.0	8.0	100	62	1600	4500	Black
RND 425-00083	10.0	7.5	100	60	1900	5700	Black
RND 425-00084	12.0	9.0	100	67	1900	5700	Black
RND 425-00085	4.0	2.0	200	30	3500	6800	White
RND 425-00086	6.0	4.0	200	37	2700	8100	White
RND 425-00087	8.0	5.0	100	48	1900	5700	White
RND 425-00088	10.0	8.0	100	62	1600	4500	White
RND 425-00089	10.0	7.5	100	60	1900	5700	White
RND 425-00090	12.0	9.0	100	67	1900	5700	White