


TWS Wiring Base



RND 430-00070

Base di cablaggio

*Wiring base
Base de cablage
Verdrahtungssockel
Base de conexionado*

| | |
|--|---|
| CUPOLA <i>DOME DOME HAUBE CÚPULA</i> | PC |
| GHIERA <i>RING BAGUE RING CONTERA</i> | PC |
| COLORI DISPONIBILI <i>AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES</i> |  |
| TENSIONE DI ALIMENTAZIONE <i>VOLTAGE TENSION SPANNUNG TENSIÓN</i> | 24 Vdc/Vac – 110Vac – 240Vac |
| SERVIZIO <i>OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO</i> | ∞ |
| GRADO IP <i>IP RATING DEGRE IP SCHUTZART GRADO IP</i> | IP66 |
| TEMPERATURA DI FUNZIONAMENTO <i>OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR TEMPERATURA DE FUNCIONAMIENTO</i> | -30°C+50°C |
| VIBRAZIONI <i>VIBRATIONS VIBRATIONS VIBRATIONEN VIBRACIONES</i> | INDUSTRIAL CEI 60068-2-6 SINE |
| CERTIFICAZIONI, OMOLOGAZIONI <i>CERTIFICATIONS, APPROVALS CERTIFICATIONS, HOMOLOGATIONS PRODUKTZERTIFIKATE, ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES</i> | CE, UKCA |
| FISSAGGIO <i>MOUNTING FIXATION FIXIERUNG FIJACIÓN</i> | Tramite ghiera <i>Ring Bague Ring Contera</i> |

TWS Wiring Base



DISEGNO

TECHNICAL DRAWING
DESSIN
TECHNISCHE ZEICHNUNG
DIBUJO TECNICO

