





A-A (1:1)





ISO (1:1)




B-B (1:1)




C-C (1:1)



Z (2:1)



Y (2:1)



For Version with enclosed gasket  
Protection class IP40. To achieve protection class IP65,  
the enclosed gasket must be mounted correctly. The gasket must not be  
stretched or compressed in the corners. Ends cut obliquely and glued, so  
that the cut ends are pressed together by the spring pressure.

SPECIFICATION	
RND NUMBER	RND 455-01421
Distrelec NUMBER	303-75-365
RND BAR CODE NUMBER	0653415230458
Product text English	Enclosure PC GREY. IP66.68
Outer Dimensions	209.7 x 139.8 x 60mm
Inner dimension length	180.6 x 131.6 x 52.9mm
Material	Polycarbonate
Colour	light grey. similar to RAL 7035
Lid	N/A
Wall brackets	N/A
Colour	light grey. similar to RAL 7035
Protection class	IP66 IP68 IK07