

# Brushless Axial DC Fan

60 x 60 x 15 mm, 12 V, 2.16 W



## FEATURES:

Single impeller fan with low noise characteristic

Suitable for most application

## SPECIFICATION:

Dimensions	60 x 60 x 15 mm
Rated voltage	12 V
Rated current	0.10 A
Volumetric flow rate max.	36.5 m <sup>3</sup> /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	32 dBA
Power consumption	1.2 W
Revolution speed	4000 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	44 g
Max. air flow	0.61 m <sup>3</sup> /min 21.7 CFM
Max. static pressure	4.1 mm-H <sub>2</sub> O 0.16 In-H <sub>2</sub> O



Art. Nr.

RND 460-00008

