

Brushless Axial DC Fan

60 x 60 x 25 mm, 24 V, 3.84 W



FEATURES:

Single impeller fan with low noise characteristic

Suitable for most application

SPECIFICATION:

Dimensions	60 x 60 x 25 mm
Rated voltage	24 V
Rated current	0.16 A
Volumetric flow rate max.	57 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	40 dBA
Power consumption	3.84 W
Revolution speed	5000 rpm
Temperature range	-10...+70 °C
Voltage	14...26.4 V
Weight	57 g
	0.95 m ³ /min
Max. air flow	33.60 CFM
	6.30 mm-H ₂ O
Max. static pressure	0.25 In-H ₂ O



Art. Nr.

RND 460-00016

