

Brushless Axial DC Fan

120 x 120 x 25 mm, 12 V, 3.36 W



FEATURES:

Single impeller fan with low noise characteristics

Suitable for most applications

SPECIFICATION:

Dimensions	120 x 120 x 25 mm
Rated voltage	12 V
Rated current	0.28 A
Volumetric flow rate max.	145.2 m ³ /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	36 dBA
Power consumption	3.36 W
Revolution speed	2500 rpm
Temperature range	-10...+70 °C
Voltage	7.0...13.2 V
Weight	152 g
	2.42 m ³ /min
Max. air flow	85.50 CFM
	5.00 mm-H ₂ O
Max. static pressure	0.20 In-H ₂ O



Art. Nr.

RND 460-00033

