

# Brushless Axial DC Fan

120 x 120 x 25 mm, 24 V, 4.80 W



## FEATURES:

Single impeller fan with low noise characteristics  
Suitable for most applications

## SPECIFICATION:

Dimensions	120 x 120 x 25 mm
Rated voltage	24 V
Rated current	0.20 A
Volumetric flow rate max.	145.2 m <sup>3</sup> /h
Bearing	Two Ball Bearing
Colour	Black
Material	PBT UL94V0
Max. noise	36 dBA
Power consumption	4.80 W
Revolution speed	2500 rpm
Temperature range	-10...+70 °C
Voltage	14.0...26.4 V
Weight	152 g
	2.42 m <sup>3</sup> /min
Max. air flow	85.50 CFM
	5.00 mm-H <sub>2</sub> O
Max. static pressure	0.20 In-H <sub>2</sub> O



Art. Nr.

RND 460-00035

