

Crimp terminal socket

red



FEATURES:

Double crimp with copper sleeve on barrel

SPECIFICATION:

Cross-section	0.5...1.5 mm ²
Colour	red
Diameter	3.9 mm
Material	Brass
Insulation material	Nylon
Surface material	Tin-plated
Voltage	600 V
Thickness	0.4 mm
Temperature range	max. +105 °C



Art. Nr.

RND 465-00092

