

Power Strip

LED, 6xT23, 3 m, Type 23/Protective contact



Reconnectable with internal supply terminals

Impact resistant and halogen-free case

Flexible positioning in racks, rear walls and housing frame

Fastening clips included

In accordance with the Swiss Ordinance on Low-Voltage Electrical Equipment (CVEO), approved by the Swiss Federal Inspectorate for Heavy Current Installations

SPECIFICATION:

No. of USB	2-port (5 VDC/2.1 A)
No. of sockets	6
Socket type	T23
Colour	black
Cable length	3 m
Plug type	Type 23/Protective contact
Rated output	4 kW
Load capacity	16 A/230 VAC
Dimensions L x W x H	433 x 44.4 x 44.45 mm
Socket arrangement	Lengthwise
Connecting cable	H05VV-F. 3G 1.5 mm ²
Material	Aluminium/Polypropylene
Assembly type	19" System
Mounting	Horizontal/Vertical



Art. Nr.

RND 465-00218

