

Power Strip


8xC13, 3 m, Type 12/Protective contact



With 10 A protector (thermo fuse)
Reconnectable with internal supply terminals
Impact resistant and halogen-free case
Flexible positioning in racks, rear walls and housing frame
Fastening clips included

SPECIFICATION:

No. of sockets	8
Socket type	C13
Colour	black
Cable length	3 m
Plug type	Type 12/Protective contact
Rated output	2.5 kW
Load capacity	10 A/230 VAC
Dimensions L x W x H	434 x 44.4 x 44.45 mm
Socket arrangement	Transverse
Connecting cable	H05VV-F, 3G 1 mm ²
Material	Aluminium/Polypropylene
Assembly type	19" System
Mounting	Horizontal/Vertical
Certification	S+ ESTI 17.0836



Art. Nr.
RND 465-00223

