

Butt Splice Connectors

Nylon insulated



SPECIFICATION:

Material	Copper
Surface material	Tin-plated
Max temperature	+105 °C
Colour	Yellow
Cross-section	0.2...0.5 mm ²
Width (D)	2.3 mm
Thickness (t)	0.4 mm
Length (L)	20 mm
Diameter (d)	1 mm

