


# Partially Insulated Ring Terminal



## Specification

|                           |           |
|---------------------------|-----------|
| Terminal Material         | Copper    |
| Terminal Copper Thickness | 0.75      |
| Insulation Material       | Polyamide |
| Max Temperature           | 105 °C    |
| Max Voltage               | 600 V     |
| Max Current               | 19 A      |
| Wire Range                | 22-16 AWG |

## Drawing



|    |          |
|----|----------|
| d2 | 4.30 mm  |
| B  | 6.60 mm  |
| L  | 20.40 mm |
| D  | 4.50 mm  |
| E  | 10.50 mm |
| t1 | 0.60 mm  |

Art. Nr.  
RND 465-01355