


Partially Insulated Blade Terminal



Specification

Terminal Material	Copper
Terminal Copper Thickness	0.75 mm
Insulation Material	PVC
Max Temperature	75 °C
Max Voltage	600 V
Max Current	19 A
Wire Range	22-16 AWG

Drawing



B	3 mm
L	21 mm
D	4.30 mm
E	10 mm
t1	0.80 mm

Art. Nr.
RND 465-01361