


# Partially Insulated Blade Terminal



## Specification

Terminal Material	Copper
Insulation Material	PVC
Terminal Copper Thickness	1 mm
Max Temperature	75 °C
Max Voltage	600 V
Max Current	48 A
Wire Range	12-10 AWG

## Drawing



B	4.60 mm
L	26.50 mm
D	6.70 mm
E	13.60 mm
t1	0.80 mm

Art. Nr.  
RND 465-01363