


# Partially Insulated Lipped Blade Terminal



## Specification

Terminal Material	Copper
Insulation Material	PVC
Terminal Copper Thickness	0.80 mm
Max Temperature	75 °C
Max Voltage	600 V
Max Current	19 A
Wire Range	22-16 AWG

## Drawing



B	4.60 mm
L	27.80 mm
D	4.30 mm
E	10 mm
t1	0.80 mm
F	17.50 mm
B1	2.20 mm

Art. Nr.  
RND 465-01365