


Partially Insulated Lipped Blade Terminal



Specification

Terminal Material	Copper
Insulation Material	PVC
Terminal Copper Thickness	0.80 mm
Max Temperature	75 °C
Max Voltage	600 V
Max Current	27 A
Wire Range	16-14 AWG

Drawing



B	4.60 mm
L	28.30 mm
D	4.70 mm
E	10.70 mm
t1	0.80 mm
F	17.50 mm
B1	2.20 mm

Art. Nr.
RND 465-01366