

LSF Data cable

Grey, Shielded, 2 pairs x 2 cores



CORE IDENTIFICATION:

- 1 Pair: ●● Black + Red
2 Pair: ●○ Green + White

APPLICATION:

LSF (Low Smoke and Fume) cable is suitable for instrumentation, computer and security applications, point of sale, control systems, and RS232 applications.

SPECIFICATION:

Cable type	Data cable
Nominal overall diameter	4.2 mm
Cores	2 pairs x 2 cores
Core colours	black/green/red/white
Packaging	Sold by reel
Conductor	Stranded tinned copper
Sheath colour	grey
Shielding	shielded
Shielding material	Aluminium foil
Conductor insulation	PE (Polyethylene)
Original packaging	100 m
Sheath	LSF (Low Smoke and Fume)
Nominal Diameter of Strands	0.24 mm
Rated voltage	300 V
Capacitance	114.8 pF/m
Conductor resistance	65.3 Ω/km
Temperature range (Fixed)	-20...+80 °C
Standards	RS232 and UL1581

Art. Nr.

RND 475-00633