



Specification:

Characteristics	Unit	Limits	Analysis Methods
Relative viscosity (formic acid 90%)	-	46.7 – 52.6	LAB782.3
Moisture content at packing	%	≤ 0.35	LAB785.3
Yellow Index on pellets	-	≤ 1	LAB787.3
Count of black spots: > 1 mm ≤ 1 mm and > 0.3 mm	Black spots / kg Black spots / kg	0 ≤ 5	LAB781.3
Granulometry	g / 100 chips	2.75 – 3.25	LAB791.3

Indication:

Characteristics	Unit	Limits	Analysis Methods
Index of viscosity (sulfuric acid 96%)	ml / g	144 – 153	Ed.2 31.05.99
Relative viscosity (sulfuric acid 96%)	-	2.63 – 2.75	Ed.2 31.05.99
Index of viscosity (formic acid 90%)	ml / g	133 – 143	Ed.2 31.05.99

Physical Properties:

Appearance	Solid, white quasi cylindrical chips
Melting temperature	About 265 °C (DSC)
Solidification temperature	About 220 °C (DSC)
Bulk density	0.6 – 0.7 kg/dm ³
Density	1.14 kg/dm ³

Nylon Cable Ties



Product Range:

Art. Nr.	Width	Colour	Length
RND 475-00653	2.6 mm	Black	80 mm
RND 475-00654	2.6 mm	Natural	80 mm
RND 475-00655	2.5 mm	Black	100 mm
RND 475-00656	2.5 mm	Natural	100 mm
RND 475-00657	2.5 mm	Blue	100 mm
RND 475-00658	2.5 mm	Green	100 mm
RND 475-00659	2.5 mm	Red	100 mm
RND 475-00660	2.5 mm	Yellow	100 mm
RND 475-00661	2.5 mm	Black	120 mm
RND 475-00662	2.5 mm	Natural	120 mm
RND 475-00663	2.5 mm	Black	150 mm
RND 475-00664	2.5 mm	Natural	150 mm
RND 475-00665	2.5 mm	Black	200 mm
RND 475-00666	2.5 mm	Natural	200 mm
RND 475-00667	3.6 mm	Black	140 mm
RND 475-00668	3.6 mm	Natural	140 mm
RND 475-00669	3.6 mm	Black	150 mm
RND 475-00670	3.6 mm	Natural	150 mm
RND 475-00671	3.6 mm	Black	180 mm
RND 475-00672	3.6 mm	Natural	180 mm
RND 475-00673	3.6 mm	Black	200 mm
RND 475-00674	3.6 mm	Natural	200 mm
RND 475-00675	3.6 mm	Black	280 mm
RND 475-00676	3.6 mm	Natural	280 mm
RND 475-00677	3.6 mm	Black	300 mm
RND 475-00678	3.6 mm	Natural	300 mm
RND 475-00679	3.6 mm	Black	370 mm
RND 475-00680	3.6 mm	Natural	370 mm
RND 475-00681	4.8 mm	Black	200 mm
RND 475-00682	4.8 mm	Natural	200 mm
RND 475-00683	4.8 mm	Black	250 mm
RND 475-00684	4.8 mm	Natural	250 mm
RND 475-00685	4.8 mm	Black	300 mm
RND 475-00686	4.8 mm	Natural	300 mm
RND 475-00687	4.8 mm	Blue	300 mm
RND 475-00688	4.8 mm	Green	300 mm
RND 475-00689	4.8 mm	Red	300 mm
RND 475-00690	4.8 mm	Yellow	300 mm
RND 475-00691	4.8 mm	Black	360 mm
RND 475-00692	4.8 mm	Natural	360 mm
RND 475-00693	4.8 mm	Black	370 mm
RND 475-00694	4.8 mm	Natural	370 mm
RND 475-00695	4.8 mm	Black	400 mm
RND 475-00696	4.8 mm	Natural	400 mm
RND 475-00697	4.8 mm	Black	450 mm
RND 475-00698	4.8 mm	Natural	450 mm
RND 475-00699	7.2 mm	Black	150 mm
RND 475-00700	7.2 mm	Natural	150 mm

Nylon Cable Ties



Art. Nr.	Width	Colour	Length
RND 475-00701	7.2 mm	Black	200 mm
RND 475-00702	7.2 mm	Natural	200 mm
RND 475-00703	7.2 mm	Black	250 mm
RND 475-00704	7.2 mm	Natural	250 mm
RND 475-00705	7.2 mm	Black	300 mm
RND 475-00706	7.2 mm	Natural	300 mm
RND 475-00707	7.2 mm	Black	370 mm
RND 475-00708	7.2 mm	Natural	370 mm
RND 475-00709	7.2 mm	Black	380 mm
RND 475-00710	7.2 mm	Natural	380 mm
RND 475-00711	9 mm	Black	450 mm
RND 475-00712	9 mm	Natural	450 mm
RND 475-00713	9 mm	Black	800 mm
RND 475-00714	9 mm	Natural	800 mm