


40 Watt On/Off LED Driver



Features:

- Fully approved to all lighting specifications
- Output constant voltage
- High efficiency up to 86%
- Built in Active PFC function
- ErP Compliant
- Protections: Short circuit/ over loading/over temperature/ over Voltage
- Cooling by free air convection
- IP67 design for outdoor installation
- Input Surge Protection: 2KV line-line
- Low noise and Ripple
- 5 years warranty, High efficiency for longer life



Models

RND 500-00058

RND 500-00059

Output Specifications

Output Voltage	12V	24V
Voltage Accuracy	±5%	
Output Current	3.34A	1.67A
Rated Power	40W	

Input Specifications

Input Voltage	220-240VAC
Frequency Range	47-63Hz
Full Load Efficiency (Typ.)	86%
Power Factor Correction	>0.95, Full Load 230V/50Hz
Input Current	0.25A Max
Inrush Current	0.16A @Full Load, 230VAC
Inrush Current (T50% value)	50A, Inrush current width 380µs
No Load Power Consumption	≤0.5W

Protection

Over Load	Min: 110% Max: 150% Hiccup Auto Recovery
Short Circuit	Hiccup Auto Recovery
Over Temperature	Protection type: Auto Restore

Environment

Working TEMP.	-20~+75°C/TC Mac- 75°C
Working Humidity	20-90% RH, non-condensing
Life Time	>30,000h @40°C

Art. Nr.302-94-968 & 302-94-969

RND 500-00058 & RND 500-00059

40 Watt On/OffLED Driver



Storage Temperature

-20~+85°C

Safety & EMC

Safety standards

EN61347-1, EN61347-2-13

EMI

EEN 55015, EN 61000-3-2, EN 61000-3-3

EMS

EN61000-4-2,3,4,5,6,8,11, EN 61547

Other Specifications

Size

148 x 42 x 33 mm

Packing

355 x 320 x 275 mm (20PCS)

Weight

0.280Kg

Mechanical Specifications

