LED Work Light

Features

- Versatile foldable lamp with 5 light settings, magnetic base & robust design
- This compact LED work light with tough body and anti-slip design is ideal for
- automotive and repair work, camping, hiking and as an emergency torchServes as both a powerful strip light and a directional torch
- 24 COB LEDs
- Lightweight & portable with foldable design
- Five lighting modes
- Emergency red light settings
- Hands-free lighting magnetic base & hook
- Up to 12hrs run time
- Water resistant (IP44)

Specification



Voltage	3.7 V
Light Specification	18 White LEDs / 8 Red LEDs, 3W, 5000-6000K
Light Settings	High / Low / Flashlight (Top) / Red / Flashing Red
Battery	18650, < 1200 mAH
Light Output	350 lm
	High: Approx. 3 hrs
Usage Time	Low: Approx. 10-12 hrs
	Red & Flashing: Approx. 12 hrs
Dimensions	14.8 x 4.7cm (folded)
Cable Length	1 m
Base Type	Magnetic
Waterproofing	IP44

Instructions

- Connect the cable to the lamp and then to a USB plug or socket, charge for 3 hours.
- Switch the lamp on by pressing the power button, press the power button again to switch light setting. The lamp is now ready to use.
- The lamp can either be used cordless, attached to a computer/laptop via USB or attached to a mains adaptor and plugged into an electrical socket.