

# LED Task Lamp with Dimmer



## Features

- Shadow-free light with no heat emission
- Robust metal design and steady long reach arm
- Inbuilt 3-step dimmer
- Wide lamp head, perfect for lighting large workspaces
- Includes table clamp
- A long-reach LED task lamp ideal for a workshop, office, or home
- Perfect for lighting up larger workspaces, with the flexibility of an inbuilt dimmer feature



## Specification

Light Source	112 LEDs
Energy Consumption	21 W
Lumens	1618
Colour Temperature	6000 - 7000 K
CRI	80
Voltage	220 - 240 V, 50 Hz
Cable	1.6 m

**Art. Nr.**  
**RND 515-00001**