

# LED Task Lamp with Dual Dimmer Function



## Features

- Shadow free light with no heat emission
- Dual dimmer function from soft white to daylight
- Wide lamp head, perfect for lighting large workspaces
- Includes table clamp
- A long-reach LED task lamp with 3 lighting modes plus dimmer function
- The light settings provide a range of options from soft white to cool daylight, this versatility makes it ideal for workshop, office, or home



## Specification

Light Source	84 LEDs
Energy Consumption	18 W
Lumens	2000
Colour Temperature	6500 K
CRI	80
Voltage	220 - 240 V, 50 Hz
Cable	1.4 m

**Art. Nr.**  
**RND 515-00005**