Side Cutting Pliers





DESCRIPTION:

Side cutters for professionals with very slim, tapered head, for finest operations

Pliers made from high grade special steel for extremely high requirements

By precision inductiv hardness process blades achieve up to 65 HRC

Box joint - double leaf spring

Precise jaw adjustment without backlash

High gloss steel polished surface

Ergonomically formed bicoloured hand guard - dissipative anti-slide material

The pliers have been tested with good results by several test laboratories adequate to DIN EN 61340-5-1, DIN 61340-2-1, DIN 61340-2-3 for work in ESD protected areas

SPECIFICATION:

125 mm
11 mm
7.5 mm
13 mm
Without - Full flush cut
Ø 1.5 mm
Ø 0.8 mm
-
65 g

Art. Nr. RND 550-00252

