Snipe Nose Pliers





DESCRIPTION:

Snipe nose pliers for professionals with straight, serrated jaws

Special pliers made from high grade special steel for extremely high requirements

For gripping, bending and holding

Box joint - double leaf spring

Precise jaw adjustment without backlash

High gloss steel polished surface

Ergonomically formed bicoloured hand guard - dissipative anti-slide material

The pliers have been tested with good results by several test laboratories adequate to DIN EN 61340-5-1, DIN 61340-2-1, DIN 61340-2-3 for work in ESD protected areas

SPECIFICATION:

Length	140 mm
A - Head width	10 mm
B - Head length	32 mm
C - Head thickness	6.5 mm
D - Jaws thickness	2 mm
E - Jaws width	1 mm
Weight	68 g

Art. Nr. RND 550-00262

