RJ45 Open-Pass Modular Plug 🏌



Features

- Allows wires to be fully inserted and pass through holes to verify conductor order before crimping
- \bullet Works on CAT6 solid or stranded wires AWG 26-24 / 23
- 3 prong contacts for secure connection with wires
- 50u gold plated contacts to prevent erosion and extend plug life




Specification

Gender	Plug
LAN Category	CAT6
Connector Type	RJ45
Number of Contacts	3
Number of Positions	3
Mounting Type	Cable Mount
Length	0.887" (22.5 mm ± 0.1mm) / Piece
Weight	1.6 g / Piece
Quantity	50 pcs / Pack

Material Specification

Housing Material	Polycarbonate (PC)
Contact Material	Phosphor Bronze
Contact Plating	Gold 50u



0.50±8.03

"3" : 3 PRONGS FOR STRANDED & SOLID WIRE

RJ45 Open-Pass Modular Plug 🖗



Accessories



Protective Cover for RJ-45 Connector RND 610-00033



Anti-Kink Sleeves RND 765-00015 - Grey RND 765-00016 - Yellow RND 765-00017 - Green RND 765-00018 - Blue RND 765-00019 - Black RND 765-00020 - White



Professional Modular Plug Crimper For RJ45 Open-Pass Plug RND 550-00344

Art Nr. RND 550-00347