

Tool Box Case with Added Storage



Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Tough fabric inlay for tool storage



Specification

IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

External Dimensions	464 x 366 x 176 mm
Internal Dimensions	426 x 290 x 159mm
Cover Depth - Bottom	45 + 114 mm
Weight	3.24 kg
Temperature Range	-30 ... 90 °C
Capacity	19.64 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.
RND 550-00509

