

# Equipment / Tool Box Case Storage



## Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free



## Specification

**IP67 RATING** **ATA 300** **MIL SPECS** DEF STAN 81-41  
STANAG 4280

External Dimensions	555x 428 x 211mm
Internal Dimensions	500 x 350 x 194mm
Cover Depth - Bottom	58 + 136 mm
Weight	3.9 kg
Temperature Range	-30 ... 90 °C
Capacity	33.95 l
Protection Rating	IP67

## Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.

RND 550-00511

