

Precision Pocket Caliper



Features

- High quality imperial / metric measurements
- Thumb wheel for accuracy and ease of use
- 4 measurements: inside, outside, depth and step
- Guide rail and locking screw to accuracy
- Hardened stainless steel, precision ground and tapped measuring surfaces



Specification

Measuring Range	0 .. 150 mm / 0 ... 6"
Resolution	0.01 mm / 0.0005"
Repeatability	0.01 mm / 0.0005"
Operating Temperature	0 ... 40°C
Storage Temperature	-10 ... 60°C
Relative Humidity	80% max.
Overall Length	228 mm

Art. Nr.
RND 555-00207