

LCD Touchscreen Soldering / Desoldering Station



Features

- Suitable for lead free soldering applications
- Variable temperature control via LCD touch screen
- Zero switching circuitry for spike suppression
- High idle stability
- Fast heat recovery
- Interchangeable handle
- Three channels for stored temperature presets



Specification

Power Supply	230 V / 50 Hz
Temperature Range	100 ... 500 °C
Dimensions (W x H x D)	180 x 105 x 195 mm
Weight	3.6 kg (Controller) / 4.5 kg (Total Weight)
Display Type	LCD, Touch Screen
Number of Channels	3
Power Rating	200 W
Standarts Met	2011/65/EU+2015/863/EU: RoHS directive 2014/30/EU: Electromagnetic Compatibility (EMC) Directive IEC 62321 EN 55014-1-1:2017 EN 55014-1-2:2015 EN 61000-3-2:2014 EN 61000-3-2:2013 EN 60335-2-45 :2002+A1 :2008+A2 :2012 EN 60335-1 :2012+AC :2014+A11 :2014+A13 :2017+A1 :2019+A2 :2019 EN 62233:2008

Accessories (Included with Soldering / Desoldering Station)



Desoldering Iron



Soldering Iron



2x Brass Wools, Soldering & Desoldering Iron Holders



Power Cord

Art. Nr.
RND 560-00264