ESD Workstation Kit with CEE 7/4 Plug



Description

Image shown for illustration purposes only.

A comprehensive, easy to install basic ESD Safe workstation kit. The Kit has workspace or enviroment needed to build a static controlled workscape or environment items such as laptops, tablets, PCB's, Computer parts, Medical equipment and audio devices.

Features

- Reflection breaking surface to reduce glare and improve operator comfort
- Prevention of sliding of delicate components thanks to excellent friction coefficient
- Heat resistance: does not melt or burn coming into contact with hot metal parts or soldering debris
- Suitable for loose laying: does not require application with adhesive
- Good resistance to scratches and excellent flexibility and comfort

Kit Includes

- 1x ESD Matting (600x1200mm) with 10mm stud in each corner
- 1x ESD Protected Area vinyl sign
- 1x Earth Bonding Plug 3x10mm Stud

.....

Test Method	Result	
Material	Static dissipative	
Thickness	2mm	
Surface	Non-shining	
Tester	ETS 406C Static Decay Meter, 3M Model 701 Test Kit for Static Control Surfaces	
Hardness (ISO 7619)	75±5 shore A	
Abrasion Resistance (ISO 4649, method A)	≤200mm ³	
Indentation (EN433)	≤0,20mm	
Cigarette Burning Resistance (EN1399)	No burn	
Chemical Resistance (EN423)	Resistant to chemical agents normally used for maintenance	
Dimensional Stability (EN424 - 6h/80°C)	≤0.4%	
Surface Resistance Top Layer (EN 100015.1-IEC61340)	About 10 ⁸ Ω	
Surface Resistance Bottom Layer (EN 100015.1-IEC61340)	About $10^5\Omega$	



ESD Workstation Kit with Euro Plug



ESD Workstation Kit contents

ESD Protected Area Sign

- \cdot Antistatic coating
- Self adhesive: 0.4mm thick PVC
- 300 x 150mm

Earth Bonding Plug 3x10mm Stud

- Incorporates a 3x10mm male stud for connection grounding wire
- · Designed to fit European standard mains plug outlets
- Neutral and mains voltage pins are plastic, earth pin is metal

Coiled Earth Lead

- · Excellent quality for use with any kind of wrist band
- · Strong connection between the cord and 10mm stud
- 10mm Stud / Banana Socket
- Special conductive wire, outer covered with non-conductive PU
- · Diameter of cord: 2.4 mm / Diameter of coil cord: 1.02 cm
- Resistivity: 1M Ohm +/- 10%

Straight Earth Lead

- Excellent quality for use with any kind of Field Service Kit or Table Mat
- Strong connection between the cord and stud
- Outer covered with non-conductive PU
- Length: 12ft
- Diameter of cord: 2.4 mm
- Resistivity : 1M Ohm +/- 10%

Fabric Adjustable Wrist Strap Hypo Allergenic

- Sky blue band
- · Adjustable for any size of wrist
- 10mm stud
- · High quality conductive interior, made of stainless steel nylon filament
- Outer side non-conductive nylon yarn
- $\cdot\,$ Conductive back plate covers the metal part to prevent allergic reaction

Test Method EN 61340-5-1

- Resistance from Band <10⁵ Ohms Test Method EN 61340-55-1
- Underside of Band <10⁴ Ohms
- Top Side of Band < 10⁶ Ohms Test Method EN 61340-5-1

Product Code	Description	Size	Additional Notes
RND 600-00140	ESD Workstation Kit with Euro Plug	Mat 600 x 1200mm	Blue colour