

Clear Vinyl Gloves



Description

- 12" Vinyl Gloves, ISO 4 Powder-Free Bulk packed
- Cleanroom packaged and double bagged
- ESD capabilities
- Suitable protection for operators and processes in the microelectronics and semiconductor industries in addition to pharmaceutical, aerospace, automotive & medical devices
- Ambidextrous bulk packed ASTM D-3577
- 5 years shelf life from date of manufacture



Size	Medium	Large	X-Large	Test Code
Width of palm (m/m)	98±2	108±2	113±2	ASTM D5250
Total Length (m/m) From tip middle finger to cuff	Min. 300	Min. 300	Min. 300	
Length of Fingers (m/m)				± 1.0
Thumb	57	60	64	
Index Finger	70	75	82	
Middle Finger	81	89	91	
Ring Finger	73	79	86	
Little Finger	56	60	63	
Circumference of Fingers (m/m)				±1.0
Thumb	74	80	82	
Index Finger	62	68	72	
Middle Finger	64	70	74	
Ring Finger	62	68	71	
Little Finger	55	62	64	
Before and after accelerated aging (70± 2°C x 72 ± 2h) Tensile Strength (Mpa)	Min . 9 Mpa	Min . 9 Mpa	Min . 9 Mpa	ASTM D5250
Before and after accelerated aging Elongation (%)	Min . 300%	Min . 300%	Min . 300%	ASTM D5250
Thickness (m/m) Finger Tip				ASTM D5250
Palm	Min . 0.05	Min . 0.05	Min . 0.05	
Cuff	Min . 0.08	Min . 0.08	Min . 0.08	
	Min . 0.05	Min . 0.05	Min . 0.05	

Clear Vinyl Gloves



Dissipative Resistivity Test Results

Inspection Item	Test Method	Result	
		Vinyl Glove	Elastic Glove
Surface Resistance (Ohms)	JIS K6911	7.45×10^1 Ohms	4.30×10^1 Ohms

Product Code	Description	Pack Size
RND 600-00190	Clear Vinyl Gloves - M	Pack of 100
RND 600-00191	Clear Vinyl Gloves - L	Pack of 100
RND 600-00192	Clear Vinyl Gloves - XL	Pack of 100