

Powder Free Disposable Nitrile Gloves



Features

- Nitrile examination glove, blue, powder free, latex free, non-sterile, textured, beaded cuff, ambidextrous, disposable
- Contents: Nitrile synthetic latex, KOH, sulphur, zinc oxide, ZDEC, ZDBC, TiO₂, colour pigment
- Free of MBT and Thiurams
- Chlorinated surface treatment
- 100 pieces per package



Physical Properties

Type Nr.	Size	Length (mm)	Width (mm)
RND 600-00269	Small	min. 240	85 ± 5
RND 600-00270	Medium	min. 240	95 ± 5
RND 600-00271	Large	min. 240	105 ± 5
RND 600-00272	Extra Large	min. 240	115 ± 5

Tensile strength (N)	AQL	Bioburden (CFU)
Before aging ≥ 6 N After aging ≥ 6 N	AQL 1,5	< 300 (CFU = colony-forming unit)

Thickness (mm)

Cuff	0.06 mm ± 0.010
Palm	0.07 mm ± 0.020
Finger	0.10 mm ± 0.020

Testing Standards

- EN 455-1 / -2 / -3 / -4
- EN 374-1 / -2 / -4 / -5
- EN 16523-1
- EN 420

Shelf Life

3 years if stored properly: store in a cool and dry place, protect from sunlight and fluorescent light. Avoid temperatures below 5 °C and higher than 35 °C

Quality Certificates

- EN ISO 13485:2016
- 93/42/EWG/EEC: Medical product of class I rule 1
- Regulation (EU) 2016/425: Personal protective equipment Cat. III
- Food Compliance acc. to EC Directive 1935/2004